



MEG 14-40-L-II


SpeechLine Wired Connection Guide

MEG 14-40-L-II



- 1 microphone ground
- 2 microphone +
- 3 microphone -
- 4 LED ground
- 5 LED


Sennheiser TeamConnect



Biamp Nexia / Tesira


Audio Input
(Nexia or Tesira)

+ - G




Biamp Logic Box

Logic inputs are activated via contact-closure or 5V TTL
Logic outputs are open-collector (40V / 500mA max. per output)



POLYCOM SoundStructure



Sennheiser electronic GmbH & Co. KG

Am Labor 1, 30900 Wedemark, Germany

www.sennheiser.com

TI 1020 v1.0